

## Series PD-10LHP

Piezoresistive differential pressure sensor capsules with optimum stability

### Features

- Optimum long-term stability
- Robust stainless-steel housing
- Front-flush, crevice-free welded diaphragm
- Very high proof pressure
- High line pressure up to 600 bar
- Optimised thermal behaviour



### Technology

- Insulated piezoresistive pressure sensor chip, encapsulated in an oil-filled metal
- Ideal for mounting with O-ring
- Typical range of output signal of 160 mV / mA

### Typical Applications

- OEM
- Industry
- Laboratory

#### Accuracy

$\pm 0,25\%$  FS


#### Long-term Stability

$\pm 0,15\%$  FS/year


#### Pressure Ranges

0...0,1 bar to 0...30 bar

Series PD-10LHP



Electrical Diagram of a PD-10LHP with compensation resistors



## Series PD-10LHP – Specifications

### Standard Pressure Ranges

Differential pressure PD		Proof pressure positive	Proof pressure negative	Sensitivity		
				min.	typ.	max.
-0,1...0,1	0...0,1	5	2,5	98	130	163
-0,3...0,3	0...0,3					
-1...1	0...1	15	7,5	40	53	66,7
	0...3	15	7,5	40	53	66,7
	0...10	50	25	12	16	20
	0...30	120	60	4	5,3	6,7
bar diff.		bar		mV / (mA × bar)		
Zero point at 0 bar differential pressure		Based on reference to zero				

### Performance

Accuracy @ RT (20...25 °C)	± 0,25 %FS typ.	Non-linearity (BFSL), pressure hysteresis, non-repeatability
	± 0,50 %FS max.	
Offset @ RT (20...25 °C)	< ± 25 mV / mA	Uncompensated
	< ± 2 mV / mA	Compensated with R3 or R4.
Compensated temperature range	-10...80 °C	Other temperature ranges between -55...150 °C are possible as an option.
Long-term stability	≤ ± 0,15 %FS	For pressure ranges > 1 bar, per year under reference conditions.
	≤ ± 1,5 mbar	For pressure ranges ≤ 1 bar, per year under reference conditions.
Line pressure	≤ 600 bar	
Line pressure dependency	< 0,01 mV / bar	For pressure ranges ≥ 1 bar
	< 0,02 mV / bar	For pressure ranges < 1 bar
Position dependency	≤ ± 3 mbar	Calibrated in vertical installation position with metal diaphragm (+) side facing downwards.
Temperature coefficient zero TCzero pre-compensated with R1 or R2	≤ ± 0,015 %FS / K	For pressure ranges ≥ 3 bar
	≤ ± 0,45 mbar / K	For pressure ranges < 3 bar
Temperature coefficient sensitivity TCsens	≤ ± 0,06 % / K	For pressure ranges ≥ 1 bar
	≤ ± 0,12 % / K	For pressure ranges < 1 bar
Temperature coefficient total bridge resistance TC-resistance	1800...3000 ppm / K	

## Series PD-10LHP – Specifications

### Electrical Data

Half-bridge configuration

Constant current supply	1 mA nominal 3 mA max.
Bridge resistance @ RT (20...25 °C)	3,5 kΩ ± 20 %
Electrical connection	Optional: Silicone wires AWG28 (0,09 mm <sup>2</sup> ), L = 100 mm
Insulation	> 100 MΩ @ 500 VDC

### Mechanical Data

Materials in contact with media

Housing and diaphragms	Stainless steel AISI 316L	
Seal ring at 600 bar line pressure	ø 15 mm × 2 mm FKM (75 Shore) -20...200 °C	For medium temperatures < -20 °C FVMQ is used.
Support ring	PTFE	

Other materials

Pressure transmitter capsule oil filling	Silicone oil
--	--------------

Further details

Diameter × height	ø 19 mm × 35 mm	See Dimensions and variants
Weight	approx. 55 g	


### Environmental conditions

Media temperature range	-40...125 °C		Operating temperature, consider o-ring. Icing not permitted.
Ambient temperature range	-40...125 °C		
Storage temperature range	-40...125 °C		
Vibration resistance	10 g, 10...2000 Hz, ± 10 mm	IEC 60068-2-6	
Shock resistance	50 g, 6 ms	IEC 60068-2-27	
Natural frequency (resonance)	> 30 kHz		
Endurance @ RT (20...25 °C)	> 10 million pressure cycles	0...100 %FS	
Dead volume change @ RT (20...25 °C)	< 10 mm <sup>3</sup>		

## Series PD-10LHP – Dimensions and variants

### Overview of Versions

PD-10LHP



### Electrical Connection

Half-open measurement bridge pin assignment

Label	Designation	Wire colour
+OUT	Positive Output	red
+IN	Positive Supply	black
-OUT	Negative Output	blue
-IN <sub>-OUT</sub>	Negative Supply (half bridge -OUT)	yellow
-IN <sub>+OUT</sub>	Negative Supply (half bridge +OUT)	white

### Customised configurations on request

- Calibration to other pressure ranges
- Calibration to other temperature ranges within -55...150 °C
- Calibration with mathematical modeling
- Housing and diaphragm made of Hastelloy C-276
- O-Rings made of other materials
- Other oil filling types
- Modifications to customer-specific applications

### Examples of similar products

- Series PD-10L: Differential pressure sensor capsule with line pressure  $\leq 200$  bar
- Series PD-10LHPX: Differential pressure sensor capsule with digital compensation electronics
- Series 10L: Pressure transducer capsule for absolute and relative pressure ranges  $\leq 200$  bar
- Series 10LHP: High-pressure transducer capsule for absolute and relative pressure ranges  $> 200$  bar
- Series 4L...9L: Pressure transducer capsule in more compact designs for absolute and relative pressure ranges  $\leq 200$  bar

## Series PD-10LHP – Analysis and Characteristic Lines

### Standard Analysis

The PD-10LHP are intended for o-ring mounting and depend on the stress isolation provided by o-rings for performance within stated specifications. This installation enables the values measured during factory testing to remain valid. If the pressure transducers are not installed free from stress, the mechanical forces may change the measured values and the stability.


Calibration sheet: Example type PD-10L					Key
<b>PD-10L / 10 bar / 10-1035-142<sup>(1)</sup> Sn 8447<sup>(2)</sup></b>					1. Type (PD-10L) and measuring range (10 bar) 2. Serial number 3. Actual test temperatures 4. Uncompensated zero offset 5. Zero offset values with calculated compensation resistor R1 (+) or R2 (-) 6. Zero offset values with calculated compensation resistors 7. Temperature zero error with calculated compensation resistors 8. Calculated compensation resistor values R1 or R2 (TCzero) and R3 or R4 (offset) 9. RB: Bridge resistance at room temperature 10. Calculated offset with compensation resistors R1 or R2 and R3 or R4 11. Sensitivity of pressure sensor at room temperature 25° C 12. Pressure test points 13. Signal change at room temperature 25° C 14. Non-linearity (best straight line through zero) 15. Non-linearity (best straight line) 16. Results of long-term stability test 17. Sensor traceability information 18. Insulation test 19. Excitation (constant current) 20. Date of test ----- Test equipment
(3) Temp [°C]	(4) Zero [mV]	(5) +1000 [mV]	(6) Comp [mV]	(7) dZero [mV]	
-9.3	3.5	1.1	1.1	-0.1	
-0.5	4.0	1.2	1.2	-0.1	
24.0	4.3	1.3	1.3	0.0	
49.3	4.8	1.3	1.3	0.1	
79.1	5.5	1.4	1.4	0.1	
COMP R1 1000 kOhm <sup>(8)</sup> R3 0.0 Ohm <sup>(8)</sup> RB 3425 Ohm <sup>(9)</sup> ZERO 1.3 mV <sup>(10)</sup> SENS 16.72 mV/bar <sup>(11)</sup> LIN (12) [bar] (13) [mV] (14) Lnorm [%Fs] (15) Lbfs [%Fs] 0.000 0.0 0.00 -0.01 2.500 41.8 0.02 0.01 5.000 83.6 0.00 0.00 7.500 125.4 -0.02 -0.01 10.000 167.2 -0.01 -0.01					
Long Term Stability Ok <sup>(16)</sup> Lot 72114-2 <sup>(17)</sup> Test 500 Volt Ok <sup>(18)</sup> Supply 1.000 mA <sup>(19)</sup> 30.11.18 <sup>(20)</sup> ----- PH02.A03D1S <sup>(20)</sup>					

#### Notes

- The indicated specifications apply only for constant current supply of 1 mA. The Pressure transducer module must not be supplied with more than 3 mA. The output voltage is proportional to the supply current. If the supply deviates from the calibration, this will cause signal shifts.
- The compensation resistors described in this data sheet are not part of the pressure transducer modules and are not included in the scope of delivery.
- It is recommended to use compensation resistors with temperature coefficients of < 50 ppm/°C for large temperature ranges. Pressure transducer module and resistors can be exposed to different temperatures.
- In addition, a maximum TC-sensitivity can be guaranteed on request or the value for the compensation resistor (R5) can be indicated. See «Electrical diagram of compensation resistors» on page 1.

### Characteristic Lines

Examples of typical characteristic curves of the temperature coefficients, normalised at 25 °C, uncompensated vs. compensated.



## Series PD-10LHP – Analysis and Characteristic Lines

### Mathematical Compensation Model

The KELLER Pressure pressure transducers of series PD-10LHP can be ordered with an optional mathematical compensation model.

The compensation model is a mathematical formula that helps to calculate the compensated pressure value of the pressure transducer. Both the pressure signal and the temperature signal of the pressure transducer are incorporated into the calculation. Polynomial functions are used as the basis for this mathematical model.

The pressure transducers are characterised in the factory in order to produce the compensation model. This involves measuring pressure and temperature signals at various pressure and temperature levels. Comparing the measured values with the known pressure and temperature values enables the calculation of the compensation coefficients of the pressure transducer. These compensation coefficients are made available to the customer along with the respective pressure transducer.



### KELLER myCalibration

#### Content

myCalibration is a digital data platform provided free of charge to KELLER Pressure customers. It provides an easy option for transferring and providing sensor calibration data.

#### Format

The calibration data is available in the standard JSON file format, which facilitates smooth integration into the customer's software. The file structure is clearly defined in a publicly accessible JSON schema. This means that the customer is able to integrate the data seamlessly into their software.

#### Access

The platform can be accessed either via a standard web browser (web view) or directly within the customer's linked software using an API. The calibration data remains available in myCalibration for 24 months.

#### Web app

Customers can access the calibration data for their sensors via a user-friendly interface. The system ensures secure authentication by asking users to enter their personal login details, thereby preventing unauthorised access to the data by third parties.

The user has the option to use various search and filter functions to download calibration data for specific sensors or mass export multiple datasets simultaneously.

#### API

Customers have the option to use the REST API for automated access and to integrate it into their processes. This means that calibration data for new sensors can be called up automatically and then processed, for example.

#### Documentation

Comprehensive technical documentation including example software is available at the following link:  
<https://mycalibration.github.io/>